



IndiLase _{Duo} 980nm-6Watts / 635nm - 200mW

• Affordable • Portable • User Friendly

Dual wavelength laser that allows you to switch from Surgical to Therapy Procedures smoothly





Easy Set-up



Preset Treatment
Parameters



Custom Option




Save and Recall Treatment Parameters



Touch Screen User Interface

Applications



Why 980nm?

- Near Infra RED laser is best suited for all dental surgical procedures and therapeutical applications.
- Versatile laser wavelength for every day dental procedures and specialized procedures like Periodontal and Aesthetic procedures.
- Near Infra RED laser light is best suited for therapeutic application due to deep penetration capabilities. Near Infra RED wavelength (980nm) is used for Intra Oral and Extra Oral pain management as well for the swelling reduction at surgical sites.

Why 635nm?

• Adding a 635nm Wavelength to your laser unit provides many advantages. Visible 635nm laser light is good for Wound Healing, Ulcer treatment and Photo Therapy application.

Technical Specifications

Treatment	Wavelength / Maximum power	980nm-6 Watts / 635nm-200mW
	Operation Mode	Continuous / Pulsed
	Pulse Duration	0.1 Sec To 4 Sec
	Pulse Interval	0.1 Sec To 4 Sec
	Pilot Beam	635 nm Red Diode Laser, <5 mW
	User Interface	7" True Color Touchscreen
General	Dimension	210(L) * 195(W)*130(H) mm
	Weight	2.5Kg
	Warranty	2 Years

Accessories



Multi - Tip Hand Piece



Teeth Whitening Prism



TMJ 20mm



Bio Stimulation Attachment



Disposable Tips

- 400um 5mm For Soft Tissue Surgery Application
- 400um 10mm For Perio Application
- 200um 15mm For Endo Application



Kevlar Cutter



Safety Goggles



Foot Pedal



Eye Protector



Transportation Bag

Optional



Dental Hand Piece



400un Bare Fiber



Advanced Endo Radial Tip (200um 15mm)



Pain Therapy Attachment

INDILASE

MEDSOL #304A / 3, Brindavan Nagar, T.N.H.B, Phase-VII, Hosur-635109, Tamilnadu, India

Customer Care +91 63829 67677 / 04344 247499 Email: info@medsol.co.in www.indilase.com